

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202836

Luminaire Tested: **LE\_6B30D010 EC6B30508027 6LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202836  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30508027 6LBWWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3230.5 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202836

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202836

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202836

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	192.9	6.0
10°-20°	573.5	17.8
20°-30°	863.4	26.7
30°-40°	882.7	27.3
40°-50°	536.1	16.6
50°-60°	150.9	4.7
60°-70°	22.9	0.7
70°-80°	7.4	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1629.8	50.4
0°-40°	2512.5	77.8
0°-60°	3199.6	99.0
0°-90°	3230.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3230.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2006	
5°	2015	193
15°	2031	574
25°	1885	863
35°	1431	883
45°	689	536
55°	150	151
65°	20	23
75°	8	7
85°	0	1
90°	0	



TEST NUMBER: P202836

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2006.5
2.5°	2006.5
5°	2014.6
7.5°	2026.8
10°	2026.8
12.5°	2034.9
15°	2030.8
17.5°	2022.8
20°	1994.4
22.5°	1953.8
25°	1884.9
27.5°	1807.9
30°	1702.5
32.5°	1576.9
35°	1430.9
37.5°	1268.8
40°	1082.2
42.5°	887.8
45°	689.1
47.5°	510.8
50°	360.8
52.5°	243.2
55°	150.0
57.5°	89.1
60°	44.6
62.5°	28.4
65°	20.2
67.5°	16.2
70°	12.1
72.5°	8.1
75°	8.1
77.5°	4.0
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)