

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203803

Luminaire Tested: **LE_6B60D010R EC6B60708030 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708030 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5028.8 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203803

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203803

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74																			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70																			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66																			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63																			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60																			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203803

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	835.8	16.6
10°-20°	1606.0	31.9
20°-30°	1460.0	29.0
30°-40°	885.0	17.6
40°-50°	201.5	4.0
50°-60°	25.7	0.5
60°-70°	11.6	0.2
70°-80°	3.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3901.8	77.6
0°-40°	4786.8	95.2
0°-60°	5013.9	99.7
0°-90°	5028.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5028.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9873	
5°	9309	836
15°	5784	1606
25°	3166	1460
35°	1403	885
45°	222	201
55°	26	26
65°	8	12
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203803

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	9873.4
2.5°	9753.5
5°	9308.6
7.5°	8590.0
10°	7674.5
12.5°	6724.8
15°	5783.6
17.5°	4928.1
20°	4209.4
22.5°	3627.6
25°	3165.6
27.5°	2755.0
30°	2352.9
32.5°	1882.2
35°	1403.1
37.5°	983.9
40°	650.2
42.5°	402.1
45°	222.5
47.5°	102.6
50°	42.8
52.5°	34.2
55°	25.6
57.5°	25.6
60°	17.1
62.5°	17.1
65°	8.5
67.5°	8.5
70°	8.5
72.5°	8.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)