

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203259

Luminaire Tested: **LE\_6B30D010 EC6B30509727 6LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203259  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30509727 6LBMH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1928.2 lumens  
Efficiency: N/A  
Efficacy: 68.9 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203259

CATALOG NUMBER: LE\_6B30D010 EC6B30509727 6LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203259

CATALOG NUMBER: LE\_6B30D010 EC6B30509727 6LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92		
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53		
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49		
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203259

CATALOG NUMBER: LE\_6B30D010 EC6B30509727 6LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.5	9.0
10°-20°	451.4	23.4
20°-30°	584.9	30.3
30°-40°	434.2	22.5
40°-50°	183.3	9.5
50°-60°	65.1	3.4
60°-70°	25.1	1.3
70°-80°	8.7	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1210.7	62.8
0°-40°	1644.9	85.3
0°-60°	1893.3	98.2
0°-90°	1928.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1928.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1908	
5°	1867	174
15°	1611	451
25°	1297	585
35°	688	434
45°	226	183
55°	69	65
65°	25	25
75°	8	9
85°	0	1
90°	0	



TEST NUMBER: P203259

CATALOG NUMBER: LE\_6B30D010 EC6B30509727 6LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1908.2
2.5°	1902.8
5°	1866.9
7.5°	1814.6
10°	1751.2
12.5°	1682.4
15°	1610.9
17.5°	1531.0
20°	1459.4
22.5°	1385.0
25°	1296.9
27.5°	1175.8
30°	1032.6
32.5°	864.6
35°	688.4
37.5°	539.8
40°	410.2
42.5°	305.6
45°	225.8
47.5°	165.2
50°	121.1
52.5°	90.9
55°	68.9
57.5°	52.4
60°	41.2
62.5°	30.2
65°	24.8
67.5°	19.2
70°	13.8
72.5°	11.0
75°	8.2
77.5°	5.5
80°	2.8
82.5°	2.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)