

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204215

Luminaire Tested: **LE_6B60D010R EC6B60708030 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708030 6LBSH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7774.3 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204215
CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204215

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204215

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.9	4.9
10°-20°	1035.2	13.3
20°-30°	1437.6	18.5
30°-40°	1568.7	20.2
40°-50°	1463.4	18.8
50°-60°	1110.7	14.3
60°-70°	608.2	7.8
70°-80°	167.3	2.2
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2853.6	36.7
0°-40°	4422.3	56.9
0°-60°	6996.4	90.0
0°-90°	7774.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7774.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4066	
5°	4032	381
15°	3689	1035
25°	3124	1438
35°	2508	1569
45°	1900	1463
55°	1241	1111
65°	608	608
75°	146	167
85°	0	2
90°	0	



TEST NUMBER: P204215

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4066.0
2.5°	4066.0
5°	4031.8
7.5°	3980.4
10°	3903.4
12.5°	3800.6
15°	3689.4
17.5°	3552.4
20°	3424.0
22.5°	3269.9
25°	3124.4
27.5°	2978.9
30°	2816.2
32.5°	2662.1
35°	2508.0
37.5°	2354.0
40°	2208.5
42.5°	2054.4
45°	1900.2
47.5°	1746.2
50°	1575.0
52.5°	1412.4
55°	1241.1
57.5°	1078.5
60°	915.9
62.5°	753.2
65°	607.8
67.5°	470.8
70°	351.0
72.5°	239.6
75°	145.5
77.5°	68.5
80°	17.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)