

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205446

Luminaire Tested: **LE_6B60D010R EC6B60708030 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708030 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8048.0 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205446

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205446

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205446

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	468.0	5.8
10°-20°	1191.4	14.8
20°-30°	1519.3	18.9
30°-40°	1575.6	19.6
40°-50°	1451.8	18.0
50°-60°	1092.0	13.6
60°-70°	589.5	7.3
70°-80°	158.2	2.0
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3178.7	39.5
0°-40°	4754.3	59.1
0°-60°	7298.0	90.7
0°-90°	8048.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8048.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5079	
5°	5002	468
15°	4249	1191
25°	3300	1519
35°	2514	1576
45°	1890	1452
55°	1223	1092
65°	590	589
75°	137	158
85°	0	2
90°	0	



TEST NUMBER: P205446

CATALOG NUMBER: LE_6B60D010R EC6B60708030 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5078.6
2.5°	5061.6
5°	5001.8
7.5°	4890.6
10°	4693.9
12.5°	4497.2
15°	4249.4
17.5°	4018.5
20°	3779.1
22.5°	3531.1
25°	3300.2
27.5°	3078.0
30°	2872.8
32.5°	2684.8
35°	2513.8
37.5°	2351.2
40°	2197.4
42.5°	2034.9
45°	1889.5
47.5°	1727.1
50°	1564.6
52.5°	1393.6
55°	1222.6
57.5°	1051.6
60°	889.2
62.5°	735.2
65°	590.0
67.5°	453.1
70°	333.5
72.5°	230.9
75°	136.8
77.5°	59.9
80°	17.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)