

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204796

Luminaire Tested: **LE_6B30D010 EC6B30508030 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508030 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4057.1 lumens
Efficiency: N/A
Efficacy: 144.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204796

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204796

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204796

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.0	3.9
10°-20°	447.0	11.0
20°-30°	672.4	16.6
30°-40°	796.8	19.6
40°-50°	793.0	19.5
50°-60°	639.2	15.8
60°-70°	386.8	9.5
70°-80°	143.6	3.5
80°-90°	21.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1276.3	31.5
0°-40°	2073.2	51.1
0°-60°	3505.4	86.4
0°-90°	4057.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4057.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1657	
5°	1650	157
15°	1583	447
25°	1460	672
35°	1276	797
45°	1033	793
55°	713	639
65°	388	387
75°	130	144
85°	17	21
90°	0	



TEST NUMBER: P204796

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1657.0
2.5°	1657.0
5°	1649.6
7.5°	1644.8
10°	1630.0
12.5°	1605.4
15°	1583.2
17.5°	1558.8
20°	1529.2
22.5°	1499.8
25°	1460.4
27.5°	1418.5
30°	1371.9
32.5°	1327.6
35°	1276.0
37.5°	1221.9
40°	1158.0
42.5°	1096.5
45°	1032.6
47.5°	961.2
50°	882.6
52.5°	801.5
55°	713.0
57.5°	634.2
60°	545.8
62.5°	467.1
65°	388.5
67.5°	314.8
70°	245.9
72.5°	184.4
75°	130.2
77.5°	83.6
80°	49.1
82.5°	29.5
85°	17.2
87.5°	7.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)