

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203397

Luminaire Tested: **LE\_6B60D010R EC6B60709030 6LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203397  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60709030 6LBMWH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5032.6 lumens  
Efficiency: N/A  
Efficacy: 80.5 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203397

CATALOG NUMBER: LE\_6B60D010R EC6B60709030 6LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203397

CATALOG NUMBER: LE\_6B60D010R EC6B60709030 6LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203397

CATALOG NUMBER: LE\_6B60D010R EC6B60709030 6LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	573.9	11.4
10°-20°	1409.0	28.0
20°-30°	1630.3	32.4
30°-40°	1042.1	20.7
40°-50°	295.5	5.9
50°-60°	52.8	1.0
60°-70°	21.6	0.4
70°-80°	7.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3613.3	71.8
0°-40°	4655.4	92.5
0°-60°	5003.6	99.4
0°-90°	5032.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5032.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6278	
5°	6166	574
15°	5053	1409
25°	3598	1630
35°	1645	1042
45°	343	295
55°	49	53
65°	21	22
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P203397

CATALOG NUMBER: LE\_6B60D010R EC6B60709030 6LBMWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6278.1
2.5°	6271.1
5°	6166.1
7.5°	5977.2
10°	5711.2
12.5°	5403.2
15°	5053.4
17.5°	4689.4
20°	4332.4
22.5°	3982.5
25°	3597.5
27.5°	3177.6
30°	2708.6
32.5°	2183.8
35°	1644.8
37.5°	1189.9
40°	825.9
42.5°	545.9
45°	343.0
47.5°	203.0
50°	119.0
52.5°	70.0
55°	49.0
57.5°	42.0
60°	35.0
62.5°	28.0
65°	21.0
67.5°	14.0
70°	14.0
72.5°	7.0
75°	7.0
77.5°	7.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)