

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204634

Luminaire Tested: **LE_6B60D010R EC6B60709030 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709030 6LBSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6924.2 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204634

CATALOG NUMBER: LE_6B60D010R EC6B60709030 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204634

CATALOG NUMBER: LE_6B60D010R EC6B60709030 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																												
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																												
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																												
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																												
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																												
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																												
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																												
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																												
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																												
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204634

CATALOG NUMBER: LE_6B60D010R EC6B60709030 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.3	3.8
10°-20°	753.5	10.9
20°-30°	1134.8	16.4
30°-40°	1350.3	19.5
40°-50°	1347.8	19.5
50°-60°	1096.1	15.8
60°-70°	674.3	9.7
70°-80°	261.2	3.8
80°-90°	41.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2152.6	31.1
0°-40°	3502.9	50.6
0°-60°	5946.8	85.9
0°-90°	6924.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6924.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2790	
5°	2782	264
15°	2675	753
25°	2470	1135
35°	2162	1350
45°	1752	1348
55°	1227	1096
65°	677	674
75°	238	261
85°	33	42
90°	0	



TEST NUMBER: P204634

CATALOG NUMBER: LE_6B60D010R EC6B60709030 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2789.8
2.5°	2793.9
5°	2781.5
7.5°	2765.1
10°	2744.6
12.5°	2707.8
15°	2674.9
17.5°	2625.6
20°	2572.4
22.5°	2523.1
25°	2469.8
27.5°	2395.9
30°	2322.1
32.5°	2252.4
35°	2162.1
37.5°	2063.6
40°	1973.4
42.5°	1862.6
45°	1751.8
47.5°	1632.9
50°	1505.6
52.5°	1374.4
55°	1226.6
57.5°	1083.1
60°	943.6
62.5°	808.2
65°	676.9
67.5°	553.9
70°	439.0
72.5°	332.2
75°	238.0
77.5°	155.9
80°	94.4
82.5°	57.4
85°	32.9
87.5°	16.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)