

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204693

Luminaire Tested: **LE_6B30D010 EC6B30508030 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508030 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4011.8 lumens
Efficiency: N/A
Efficacy: 143.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204693

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204693

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204693

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	3.8
10°-20°	436.6	10.9
20°-30°	657.5	16.4
30°-40°	782.3	19.5
40°-50°	780.9	19.5
50°-60°	635.1	15.8
60°-70°	390.7	9.7
70°-80°	151.4	3.8
80°-90°	24.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1247.2	31.1
0°-40°	2029.5	50.6
0°-60°	3445.5	85.9
0°-90°	4011.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4011.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1616	
5°	1612	153
15°	1550	437
25°	1431	657
35°	1253	782
45°	1015	781
55°	711	635
65°	392	391
75°	138	151
85°	19	24
90°	0	



TEST NUMBER: P204693

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1616.4
2.5°	1618.8
5°	1611.6
7.5°	1602.1
10°	1590.2
12.5°	1568.9
15°	1549.9
17.5°	1521.2
20°	1490.4
22.5°	1461.9
25°	1431.0
27.5°	1388.1
30°	1345.4
32.5°	1305.0
35°	1252.8
37.5°	1195.6
40°	1143.4
42.5°	1079.1
45°	1015.0
47.5°	946.0
50°	872.4
52.5°	796.2
55°	710.8
57.5°	627.5
60°	546.8
62.5°	468.2
65°	392.2
67.5°	320.9
70°	254.4
72.5°	192.5
75°	137.9
77.5°	90.4
80°	54.6
82.5°	33.2
85°	19.0
87.5°	9.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)