

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203299

Luminaire Tested: **LE\_6B60D010R EC6B60709730 6LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203299  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60709730 6LBMH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4073.4 lumens  
Efficiency: N/A  
Efficacy: 65.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203299

CATALOG NUMBER: LE\_6B60D010R EC6B60709730 6LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203299

CATALOG NUMBER: LE\_6B60D010R EC6B60709730 6LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																																				
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																																				
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																																				
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																																				
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																																				
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																																				
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																																				
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																																				
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																																				
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																																				

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203299

CATALOG NUMBER: LE\_6B60D010R EC6B60709730 6LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	368.6	9.0
10°-20°	953.5	23.4
20°-30°	1235.5	30.3
30°-40°	917.2	22.5
40°-50°	387.2	9.5
50°-60°	137.5	3.4
60°-70°	53.1	1.3
70°-80°	18.4	0.5
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2557.6	62.8
0°-40°	3474.8	85.3
0°-60°	3999.5	98.2
0°-90°	4073.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4073.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4031	
5°	3944	369
15°	3403	953
25°	2740	1235
35°	1454	917
45°	477	387
55°	145	138
65°	52	53
75°	18	18
85°	0	2
90°	0	



TEST NUMBER: P203299

CATALOG NUMBER: LE\_6B60D010R EC6B60709730 6LBMH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4031.0
2.5°	4019.4
5°	3943.8
7.5°	3833.2
10°	3699.5
12.5°	3554.1
15°	3402.9
17.5°	3234.1
20°	3082.9
22.5°	2925.9
25°	2739.8
27.5°	2483.8
30°	2181.2
32.5°	1826.5
35°	1454.2
37.5°	1140.1
40°	866.8
42.5°	645.6
45°	477.0
47.5°	349.0
50°	256.0
52.5°	192.0
55°	145.4
57.5°	110.5
60°	87.2
62.5°	64.0
65°	52.4
67.5°	40.8
70°	29.1
72.5°	23.2
75°	17.5
77.5°	11.6
80°	5.9
82.5°	5.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)