

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204382

Luminaire Tested: **LE\_6B30D010 EC6B30508030 6LBSGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204382  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30508030 6LBSGPH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3529.4 lumens  
Efficiency: N/A  
Efficacy: 126.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204382

CATALOG NUMBER: LE\_6B30D010 EC6B30508030 6LBSGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204382

CATALOG NUMBER: LE\_6B30D010 EC6B30508030 6LBSGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204382

CATALOG NUMBER: LE\_6B30D010 EC6B30508030 6LBSGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.3	4.4
10°-20°	433.2	12.3
20°-30°	631.9	17.9
30°-40°	720.6	20.4
40°-50°	691.2	19.6
50°-60°	529.4	15.0
60°-70°	290.5	8.2
70°-80°	77.2	2.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1219.4	34.6
0°-40°	1940.0	55.0
0°-60°	3160.6	89.5
0°-90°	3529.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3529.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1639	
5°	1626	154
15°	1538	433
25°	1372	632
35°	1152	721
45°	898	691
55°	593	529
65°	292	290
75°	68	77
85°	0	1
90°	0	



TEST NUMBER: P204382

CATALOG NUMBER: LE\_6B30D010 EC6B30508030 6LBSGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1639.2
2.5°	1635.0
5°	1626.5
7.5°	1613.9
10°	1596.9
12.5°	1567.2
15°	1537.6
17.5°	1503.8
20°	1465.6
22.5°	1419.0
25°	1372.4
27.5°	1325.8
30°	1266.5
32.5°	1211.4
35°	1152.1
37.5°	1092.9
40°	1033.5
42.5°	970.0
45°	898.0
47.5°	826.0
50°	749.8
52.5°	669.2
55°	593.0
57.5°	516.8
60°	436.2
62.5°	360.0
65°	292.2
67.5°	224.5
70°	165.2
72.5°	110.1
75°	67.8
77.5°	29.6
80°	8.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)