

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203598

Luminaire Tested: **LE\_6B60D010R EC6B60708035 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203598  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60708035 6LBMMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6140.3 lumens  
Efficiency: N/A  
Efficacy: 98.2 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203598

CATALOG NUMBER: LE\_6B60D010R EC6B60708035 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203598

CATALOG NUMBER: LE\_6B60D010R EC6B60708035 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203598

CATALOG NUMBER: LE\_6B60D010R EC6B60708035 6LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	423.2	6.9
10°-20°	1133.6	18.5
20°-30°	1522.2	24.8
30°-40°	1248.7	20.3
40°-50°	749.8	12.2
50°-60°	498.3	8.1
60°-70°	334.0	5.4
70°-80°	179.8	2.9
80°-90°	50.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3079.1	50.1
0°-40°	4327.7	70.5
0°-60°	5575.9	90.8
0°-90°	6140.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6140.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4582	
5°	4505	423
15°	4040	1134
25°	3354	1522
35°	1982	1249
45°	948	750
55°	550	498
65°	339	334
75°	169	180
85°	42	51
90°	0	



TEST NUMBER: P203598

CATALOG NUMBER: LE\_6B60D010R EC6B60708035 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4581.6
2.5°	4547.8
5°	4505.4
7.5°	4412.2
10°	4302.1
12.5°	4166.6
15°	4039.6
17.5°	3887.1
20°	3734.8
22.5°	3565.4
25°	3353.6
27.5°	3099.6
30°	2760.9
32.5°	2379.8
35°	1981.8
37.5°	1643.0
40°	1355.0
42.5°	1126.4
45°	948.5
47.5°	804.5
50°	702.9
52.5°	618.2
55°	550.5
57.5°	491.2
60°	440.4
62.5°	381.1
65°	338.8
67.5°	288.0
70°	245.6
72.5°	203.2
75°	169.4
77.5°	135.5
80°	101.6
82.5°	76.2
85°	42.4
87.5°	17.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)