

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202940

Luminaire Tested: **LE_6B30D010 EC6B30508030 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508030 6LBWGPH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2458.8 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202940

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P202940

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82				82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74				74
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67				67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61				61
6	81	71	64	59	80	70	63	59	68	62	58	67	62	58	65	61	57	56				56
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51				51
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47				47
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43				43
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40				40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202940

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.4	6.4
10°-20°	441.5	18.0
20°-30°	631.6	25.7
30°-40°	629.6	25.6
40°-50°	401.0	16.3
50°-60°	147.9	6.0
60°-70°	37.0	1.5
70°-80°	11.2	0.5
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1230.5	50.0
0°-40°	1860.1	75.7
0°-60°	2408.9	98.0
0°-90°	2458.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2458.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1671	
5°	1663	157
15°	1570	441
25°	1379	632
35°	1024	630
45°	516	401
55°	156	148
65°	34	37
75°	8	11
85°	0	2
90°	0	



TEST NUMBER: P202940

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1671.1
2.5°	1671.1
5°	1662.6
7.5°	1645.8
10°	1624.6
12.5°	1599.2
15°	1569.6
17.5°	1531.5
20°	1489.2
22.5°	1442.6
25°	1379.2
27.5°	1311.5
30°	1222.6
32.5°	1129.6
35°	1023.9
37.5°	896.9
40°	765.8
42.5°	638.9
45°	516.1
47.5°	406.1
50°	304.6
52.5°	224.2
55°	156.5
57.5°	101.5
60°	67.8
62.5°	46.5
65°	33.9
67.5°	25.4
70°	21.1
72.5°	12.8
75°	8.5
77.5°	8.5
80°	4.2
82.5°	4.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)