

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204525

Luminaire Tested: **LE_6B60D010R EC6B60708035 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708035 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7008.6 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204525

CATALOG NUMBER: LE_6B60D010R EC6B60708035 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204525

CATALOG NUMBER: LE_6B60D010R EC6B60708035 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88	88	88	88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76	76	76	76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65	65	65	65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50	50	50	50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44	44	44	44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39	39	39	39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35	35	35	35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32	32	32	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29	29	29	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204525

CATALOG NUMBER: LE_6B60D010R EC6B60708035 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	291.8	4.2
10°-20°	828.0	11.8
20°-30°	1231.7	17.6
30°-40°	1433.2	20.4
40°-50°	1397.0	19.9
50°-60°	1074.5	15.3
60°-70°	594.0	8.5
70°-80°	157.3	2.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2351.4	33.6
0°-40°	3784.7	54.0
0°-60°	6256.1	89.3
0°-90°	7008.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7008.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3092	
5°	3074	292
15°	2932	828
25°	2674	1232
35°	2301	1433
45°	1812	1397
55°	1199	1075
65°	595	594
75°	133	157
85°	0	1
90°	0	



TEST NUMBER: P204525

CATALOG NUMBER: LE_6B60D010R EC6B60708035 6LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3091.8
2.5°	3091.8
5°	3074.0
7.5°	3047.4
10°	3029.6
12.5°	2976.2
15°	2931.9
17.5°	2887.4
20°	2825.2
22.5°	2763.0
25°	2674.2
27.5°	2585.4
30°	2496.5
32.5°	2398.8
35°	2301.0
37.5°	2176.6
40°	2070.0
42.5°	1954.6
45°	1812.4
47.5°	1679.1
50°	1528.1
52.5°	1368.2
55°	1199.4
57.5°	1039.5
60°	888.5
62.5°	737.4
65°	595.2
67.5°	462.0
70°	337.6
72.5°	231.0
75°	133.2
77.5°	62.2
80°	8.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)