

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205008

Luminaire Tested: **LE_6B30D010 EC6B30509030 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509030 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3244.5 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205008

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P205008

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205008

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	4.3
10°-20°	394.0	12.1
20°-30°	575.5	17.7
30°-40°	658.2	20.3
40°-50°	632.6	19.5
50°-60°	488.4	15.1
60°-70°	272.6	8.4
70°-80°	79.3	2.4
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1109.9	34.2
0°-40°	1768.1	54.5
0°-60°	2889.1	89.0
0°-90°	3244.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3244.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1490	
5°	1477	140
15°	1398	394
25°	1251	575
35°	1054	658
45°	825	633
55°	548	488
65°	273	273
75°	69	79
85°	2	3
90°	0	



TEST NUMBER: P205008

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1490.0
2.5°	1490.0
5°	1477.4
7.5°	1471.0
10°	1450.1
12.5°	1424.9
15°	1397.6
17.5°	1370.4
20°	1330.5
22.5°	1299.0
25°	1250.8
27.5°	1202.5
30°	1154.1
32.5°	1105.9
35°	1053.5
37.5°	1001.0
40°	940.1
42.5°	885.6
45°	824.8
47.5°	755.5
50°	690.4
52.5°	619.0
55°	547.8
57.5°	474.2
60°	405.0
62.5°	335.8
65°	272.8
67.5°	214.0
70°	159.5
72.5°	111.2
75°	69.2
77.5°	35.6
80°	12.6
82.5°	4.2
85°	2.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)