

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204802

Luminaire Tested: **LE_6B30D010 EC6B30509030 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509030 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3464.9 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204802

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204802

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204802

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.1	3.9
10°-20°	381.7	11.0
20°-30°	574.2	16.6
30°-40°	680.5	19.6
40°-50°	677.2	19.5
50°-60°	546.0	15.8
60°-70°	330.3	9.5
70°-80°	122.6	3.5
80°-90°	18.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1090.0	31.5
0°-40°	1770.5	51.1
0°-60°	2993.7	86.4
0°-90°	3464.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3464.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1415	
5°	1409	134
15°	1352	382
25°	1247	574
35°	1090	681
45°	882	677
55°	609	546
65°	332	330
75°	111	123
85°	15	18
90°	0	



TEST NUMBER: P204802

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1415.1
2.5°	1415.1
5°	1408.9
7.5°	1404.6
10°	1392.0
12.5°	1371.0
15°	1352.1
17.5°	1331.1
20°	1306.0
22.5°	1280.8
25°	1247.1
27.5°	1211.5
30°	1171.6
32.5°	1133.8
35°	1089.8
37.5°	1043.5
40°	988.9
42.5°	936.4
45°	881.9
47.5°	821.0
50°	753.8
52.5°	684.5
55°	608.9
57.5°	541.8
60°	466.1
62.5°	398.9
65°	331.8
67.5°	268.8
70°	210.0
72.5°	157.5
75°	111.2
77.5°	71.4
80°	42.0
82.5°	25.2
85°	14.8
87.5°	6.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)