

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205453

Luminaire Tested: **LE\_6B60D010R EC6B60709035 6LBSLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205453  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60709035 6LBSLI1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6971.7 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205453

CATALOG NUMBER: LE\_6B60D010R EC6B60709035 6LBSLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205453

CATALOG NUMBER: LE\_6B60D010R EC6B60709035 6LBSLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60																			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47																			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39																			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36																			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205453

CATALOG NUMBER: LE\_6B60D010R EC6B60709035 6LBSLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	405.4	5.8
10°-20°	1032.1	14.8
20°-30°	1316.1	18.9
30°-40°	1364.9	19.6
40°-50°	1257.6	18.0
50°-60°	946.0	13.6
60°-70°	510.6	7.3
70°-80°	137.0	2.0
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2753.5	39.5
0°-40°	4118.4	59.1
0°-60°	6322.0	90.7
0°-90°	6971.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6971.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4400	
5°	4333	405
15°	3681	1032
25°	2859	1316
35°	2178	1365
45°	1637	1258
55°	1059	946
65°	511	511
75°	118	137
85°	0	2
90°	0	



TEST NUMBER: P205453

CATALOG NUMBER: LE\_6B60D010R EC6B60709035 6LBSLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4399.5
2.5°	4384.6
5°	4332.8
7.5°	4236.5
10°	4066.1
12.5°	3895.9
15°	3681.0
17.5°	3481.0
20°	3273.6
22.5°	3058.9
25°	2858.9
27.5°	2666.4
30°	2488.6
32.5°	2325.6
35°	2177.5
37.5°	2036.8
40°	1903.5
42.5°	1762.8
45°	1636.9
47.5°	1496.1
50°	1355.4
52.5°	1207.2
55°	1059.1
57.5°	911.0
60°	770.2
62.5°	637.0
65°	511.0
67.5°	392.5
70°	288.9
72.5°	200.0
75°	118.5
77.5°	51.9
80°	14.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)