

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203569

Luminaire Tested: **LE_6B30D010 EC6B30509730 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509730 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2211.5 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203569

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203569

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203569

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.4	6.9
10°-20°	408.3	18.5
20°-30°	548.2	24.8
30°-40°	449.7	20.3
40°-50°	270.0	12.2
50°-60°	179.4	8.1
60°-70°	120.3	5.4
70°-80°	64.7	2.9
80°-90°	18.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1109.0	50.1
0°-40°	1558.7	70.5
0°-60°	2008.2	90.8
0°-90°	2211.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2211.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1650	
5°	1623	152
15°	1455	408
25°	1208	548
35°	714	450
45°	342	270
55°	198	179
65°	122	120
75°	61	65
85°	15	18
90°	0	



TEST NUMBER: P203569

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBMMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1650.1
2.5°	1637.9
5°	1622.6
7.5°	1589.1
10°	1549.4
12.5°	1500.6
15°	1454.9
17.5°	1400.0
20°	1345.1
22.5°	1284.1
25°	1207.9
27.5°	1116.4
30°	994.4
32.5°	857.1
35°	713.8
37.5°	591.8
40°	488.0
42.5°	405.6
45°	341.6
47.5°	289.8
50°	253.1
52.5°	222.6
55°	198.2
57.5°	176.9
60°	158.6
62.5°	137.2
65°	122.0
67.5°	103.8
70°	88.5
72.5°	73.2
75°	61.0
77.5°	48.8
80°	36.6
82.5°	27.5
85°	15.2
87.5°	6.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)