

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202981

Luminaire Tested: **LE_6B60D010R EC6B60708040 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202981
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60708040 6LBWGPH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5147.2 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202981

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBWGP1

Luminous Intensity Polar Plot





TEST NUMBER: P202981

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	81	71	64	59	80	70	63	59	68	62	58	67	62	58	65	61	57	56
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202981

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.6	6.4
10°-20°	924.2	18.0
20°-30°	1322.2	25.7
30°-40°	1317.9	25.6
40°-50°	839.4	16.3
50°-60°	309.5	6.0
60°-70°	77.4	1.5
70°-80°	23.4	0.5
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2576.0	50.0
0°-40°	3893.9	75.6
0°-60°	5042.8	98.0
0°-90°	5147.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5147.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3498	
5°	3481	330
15°	3286	924
25°	2887	1322
35°	2143	1318
45°	1080	839
55°	328	310
65°	71	77
75°	18	23
85°	0	4
90°	0	



TEST NUMBER: P202981

CATALOG NUMBER: LE_6B60D010R EC6B60708040 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3498.2
2.5°	3498.2
5°	3480.6
7.5°	3445.1
10°	3400.9
12.5°	3347.8
15°	3285.8
17.5°	3206.0
20°	3117.5
22.5°	3020.0
25°	2887.2
27.5°	2745.5
30°	2559.5
32.5°	2364.6
35°	2143.2
37.5°	1877.6
40°	1603.0
42.5°	1337.4
45°	1080.5
47.5°	850.2
50°	637.6
52.5°	469.4
55°	327.8
57.5°	212.5
60°	141.8
62.5°	97.4
65°	70.9
67.5°	53.1
70°	44.2
72.5°	26.6
75°	17.8
77.5°	17.8
80°	8.9
82.5°	8.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)