

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205351

Luminaire Tested: **LE_6B60D010R EC6B60709040 6LBNLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205351
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709040 6LBNLI1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5150.3 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205351

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205351

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89																			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85																			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80																			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76																			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72																			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68																			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65																			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62																			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205351

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	974.9	18.9
10°-20°	1749.9	34.0
20°-30°	1414.9	27.5
30°-40°	815.1	15.8
40°-50°	172.3	3.3
50°-60°	14.9	0.3
60°-70°	7.3	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4139.8	80.4
0°-40°	4954.8	96.2
0°-60°	5142.0	99.8
0°-90°	5150.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5150.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11726	
5°	10924	975
15°	6357	1750
25°	3052	1415
35°	1292	815
45°	186	172
55°	15	15
65°	7	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P205351

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBNLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	11726.2
2.5°	11585.1
5°	10924.2
7.5°	9973.6
10°	8807.8
12.5°	7612.0
15°	6357.0
17.5°	5146.5
20°	4262.8
22.5°	3587.0
25°	3052.2
27.5°	2599.2
30°	2190.8
32.5°	1737.8
35°	1292.2
37.5°	898.6
40°	586.6
42.5°	356.5
45°	185.6
47.5°	74.2
50°	22.2
52.5°	22.2
55°	14.9
57.5°	14.9
60°	7.4
62.5°	7.4
65°	7.4
67.5°	7.4
70°	7.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)