

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205454

Luminaire Tested: **LE_6B60D010R EC6B60709040 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205454
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709040 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6983.3 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205454

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205454

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60																			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47																			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39																			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36																			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205454

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.1	5.8
10°-20°	1033.8	14.8
20°-30°	1318.3	18.9
30°-40°	1367.1	19.6
40°-50°	1259.7	18.0
50°-60°	947.6	13.6
60°-70°	511.5	7.3
70°-80°	137.2	2.0
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2758.2	39.5
0°-40°	4125.3	59.1
0°-60°	6332.6	90.7
0°-90°	6983.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6983.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4407	
5°	4340	406
15°	3687	1034
25°	2864	1318
35°	2181	1367
45°	1640	1260
55°	1061	948
65°	512	512
75°	119	137
85°	0	2
90°	0	



TEST NUMBER: P205454

CATALOG NUMBER: LE_6B60D010R EC6B60709040 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4406.9
2.5°	4392.0
5°	4340.1
7.5°	4243.6
10°	4073.0
12.5°	3902.4
15°	3687.2
17.5°	3486.9
20°	3279.1
22.5°	3064.0
25°	2863.8
27.5°	2670.9
30°	2492.8
32.5°	2329.5
35°	2181.1
37.5°	2040.2
40°	1906.6
42.5°	1765.8
45°	1639.6
47.5°	1498.6
50°	1357.6
52.5°	1209.2
55°	1060.9
57.5°	912.5
60°	771.6
62.5°	638.0
65°	511.9
67.5°	393.2
70°	289.4
72.5°	200.2
75°	118.8
77.5°	51.9
80°	14.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)