

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205408

Luminaire Tested: **LE_6B30D010 EC6B30508035 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508035 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4080.9 lumens
Efficiency: N/A
Efficacy: 145.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205408

CATALOG NUMBER: LE_6B30D010 EC6B30508035 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205408

CATALOG NUMBER: LE_6B30D010 EC6B30508035 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60																			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47																			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39																			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36																			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205408

CATALOG NUMBER: LE_6B30D010 EC6B30508035 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.3	5.8
10°-20°	604.1	14.8
20°-30°	770.4	18.9
30°-40°	798.9	19.6
40°-50°	736.2	18.0
50°-60°	553.7	13.6
60°-70°	298.9	7.3
70°-80°	80.2	2.0
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1611.8	39.5
0°-40°	2410.7	59.1
0°-60°	3700.6	90.7
0°-90°	4080.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4080.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2575	
5°	2536	237
15°	2155	604
25°	1674	770
35°	1275	799
45°	958	736
55°	620	554
65°	299	299
75°	69	80
85°	0	1
90°	0	



TEST NUMBER: P205408

CATALOG NUMBER: LE_6B30D010 EC6B30508035 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2575.2
2.5°	2566.6
5°	2536.2
7.5°	2479.9
10°	2380.1
12.5°	2280.5
15°	2154.8
17.5°	2037.6
20°	1916.2
22.5°	1790.5
25°	1673.5
27.5°	1560.8
30°	1456.8
32.5°	1361.4
35°	1274.6
37.5°	1192.2
40°	1114.2
42.5°	1031.9
45°	958.1
47.5°	875.8
50°	793.4
52.5°	706.6
55°	620.0
57.5°	533.2
60°	450.9
62.5°	372.9
65°	299.1
67.5°	229.8
70°	169.1
72.5°	117.0
75°	69.4
77.5°	30.4
80°	8.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)