

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202781

Luminaire Tested: **LE\_6B60D010R EC6B60709040 6LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202781  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60709040 6LBWH1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5729.3 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202781

CATALOG NUMBER: LE\_6B60D010R EC6B60709040 6LBWH1

### Luminous Intensity Polar Plot






TEST NUMBER: P202781

CATALOG NUMBER: LE\_6B60D010R EC6B60709040 6LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91																			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59																			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49																			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41																			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202781

CATALOG NUMBER: LE\_6B60D010R EC6B60709040 6LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	333.7	5.8
10°-20°	947.0	16.5
20°-30°	1388.6	24.2
30°-40°	1445.1	25.2
40°-50°	999.9	17.5
50°-60°	435.3	7.6
60°-70°	133.5	2.3
70°-80°	40.0	0.7
80°-90°	6.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2669.4	46.6
0°-40°	4114.5	71.8
0°-60°	5549.7	96.9
0°-90°	5729.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5729.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3534	
5°	3519	334
15°	3363	947
25°	3036	1389
35°	2338	1445
45°	1292	1000
55°	468	435
65°	126	134
75°	37	40
85°	7	6
90°	0	



TEST NUMBER: P202781

CATALOG NUMBER: LE\_6B60D010R EC6B60709040 6LBWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3533.8
2.5°	3541.1
5°	3518.9
7.5°	3489.1
10°	3452.0
12.5°	3415.0
15°	3363.0
17.5°	3296.1
20°	3221.9
22.5°	3140.2
25°	3036.4
27.5°	2902.8
30°	2732.0
32.5°	2553.8
35°	2338.5
37.5°	2100.9
40°	1826.2
42.5°	1551.6
45°	1291.8
47.5°	1046.8
50°	831.5
52.5°	631.0
55°	467.8
57.5°	334.1
60°	230.1
62.5°	170.8
65°	126.2
67.5°	96.5
70°	66.9
72.5°	52.0
75°	37.1
77.5°	22.2
80°	14.9
82.5°	7.4
85°	7.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)