

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203606

Luminaire Tested: **LE_6B60D010R EC6B60709050 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B60D010R EC6B60709050 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5217.6 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203606

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203606

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203606

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.6	6.9
10°-20°	963.3	18.5
20°-30°	1293.4	24.8
30°-40°	1061.0	20.3
40°-50°	637.1	12.2
50°-60°	423.4	8.1
60°-70°	283.8	5.4
70°-80°	152.8	2.9
80°-90°	43.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2616.4	50.1
0°-40°	3677.4	70.5
0°-60°	4737.9	90.8
0°-90°	5217.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5217.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3893	
5°	3828	360
15°	3433	963
25°	2850	1293
35°	1684	1061
45°	806	637
55°	468	423
65°	288	284
75°	144	153
85°	36	43
90°	0	



TEST NUMBER: P203606

CATALOG NUMBER: LE_6B60D010R EC6B60709050 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3893.1
2.5°	3864.4
5°	3828.4
7.5°	3749.2
10°	3655.6
12.5°	3540.5
15°	3432.6
17.5°	3303.0
20°	3173.5
22.5°	3029.6
25°	2849.6
27.5°	2633.8
30°	2346.0
32.5°	2022.1
35°	1683.9
37.5°	1396.0
40°	1151.4
42.5°	957.1
45°	806.0
47.5°	683.6
50°	597.2
52.5°	525.4
55°	467.8
57.5°	417.4
60°	374.2
62.5°	323.9
65°	287.9
67.5°	244.6
70°	208.8
72.5°	172.8
75°	143.9
77.5°	115.1
80°	86.4
82.5°	64.8
85°	36.0
87.5°	14.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)