

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203400

Luminaire Tested: **LE\_6B60D010R EC6B60709050 6LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203400  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B60D010R EC6B60709050 6LBMWH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5135.5 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 62.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203400

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203400

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203400

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	585.7	11.4
10°-20°	1437.9	28.0
20°-30°	1663.7	32.4
30°-40°	1063.4	20.7
40°-50°	301.5	5.9
50°-60°	53.8	1.0
60°-70°	22.0	0.4
70°-80°	7.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3687.2	71.8
0°-40°	4750.7	92.5
0°-60°	5106.0	99.4
0°-90°	5135.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5135.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6407	
5°	6292	586
15°	5157	1438
25°	3671	1664
35°	1678	1063
45°	350	302
55°	50	54
65°	21	22
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P203400

CATALOG NUMBER: LE\_6B60D010R EC6B60709050 6LBMWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6406.8
2.5°	6399.5
5°	6292.4
7.5°	6099.6
10°	5828.1
12.5°	5513.9
15°	5156.8
17.5°	4785.4
20°	4421.1
22.5°	4064.0
25°	3671.1
27.5°	3242.6
30°	2764.1
32.5°	2228.4
35°	1678.5
37.5°	1214.2
40°	842.8
42.5°	557.1
45°	350.0
47.5°	207.1
50°	121.4
52.5°	71.4
55°	50.0
57.5°	42.9
60°	35.8
62.5°	28.6
65°	21.4
67.5°	14.2
70°	14.2
72.5°	7.1
75°	7.1
77.5°	7.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)