

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203565

Luminaire Tested: **LE_6B30D010 EC6B30509035 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509035 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2566.2 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203565

CATALOG NUMBER: LE_6B30D010 EC6B30509035 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203565

CATALOG NUMBER: LE_6B30D010 EC6B30509035 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203565

CATALOG NUMBER: LE_6B30D010 EC6B30509035 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.9	6.9
10°-20°	473.8	18.5
20°-30°	636.2	24.8
30°-40°	521.8	20.3
40°-50°	313.4	12.2
50°-60°	208.2	8.1
60°-70°	139.6	5.4
70°-80°	75.1	2.9
80°-90°	21.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1286.8	50.1
0°-40°	1808.7	70.5
0°-60°	2330.3	90.8
0°-90°	2566.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2566.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1915	
5°	1883	177
15°	1688	474
25°	1402	636
35°	828	522
45°	396	313
55°	230	208
65°	142	140
75°	71	75
85°	18	21
90°	0	



TEST NUMBER: P203565

CATALOG NUMBER: LE_6B30D010 EC6B30509035 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1914.8
2.5°	1900.6
5°	1882.9
7.5°	1844.0
10°	1798.0
12.5°	1741.4
15°	1688.2
17.5°	1624.6
20°	1560.9
22.5°	1490.1
25°	1401.6
27.5°	1295.4
30°	1153.9
32.5°	994.5
35°	828.2
37.5°	686.6
40°	566.2
42.5°	470.8
45°	396.4
47.5°	336.2
50°	293.8
52.5°	258.4
55°	230.0
57.5°	205.2
60°	184.0
62.5°	159.2
65°	141.6
67.5°	120.4
70°	102.6
72.5°	85.0
75°	70.8
77.5°	56.6
80°	42.5
82.5°	31.9
85°	17.8
87.5°	7.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)