

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204696

Luminaire Tested: **LE_6B30D010 EC6B30508050 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508050 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4153.3 lumens
Efficiency: N/A
Efficacy: 148.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204696

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204696

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204696

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.6	3.8
10°-20°	452.0	10.9
20°-30°	680.7	16.4
30°-40°	809.9	19.5
40°-50°	808.4	19.5
50°-60°	657.5	15.8
60°-70°	404.5	9.7
70°-80°	156.7	3.8
80°-90°	25.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1291.2	31.1
0°-40°	2101.1	50.6
0°-60°	3567.0	85.9
0°-90°	4153.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4153.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1673	
5°	1668	159
15°	1604	452
25°	1481	681
35°	1297	810
45°	1051	808
55°	736	657
65°	406	404
75°	143	157
85°	20	25
90°	0	



TEST NUMBER: P204696

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1673.4
2.5°	1675.9
5°	1668.5
7.5°	1658.6
10°	1646.2
12.5°	1624.1
15°	1604.5
17.5°	1574.9
20°	1543.0
22.5°	1513.4
25°	1481.4
27.5°	1437.1
30°	1392.9
32.5°	1351.0
35°	1296.9
37.5°	1237.8
40°	1183.6
42.5°	1117.2
45°	1050.8
47.5°	979.4
50°	903.1
52.5°	824.4
55°	735.8
57.5°	649.6
60°	566.0
62.5°	484.8
65°	406.0
67.5°	332.2
70°	263.2
72.5°	199.4
75°	142.8
77.5°	93.5
80°	56.6
82.5°	34.5
85°	19.6
87.5°	9.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)