

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208912

Luminaire Tested: **LDSQA6A45927D010TE LARH20SP 6LSQA1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208912
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26676)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A45927D010TE LARH20SP 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3104.7 lumens
Efficiency: N/A
Efficacy: 57.1 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.48
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 54.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208912

CATALOG NUMBER: LDSQA6A45927D010TE LARH20SP 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P208912

CATALOG NUMBER: LDSQA6A45927D010TE LARH20SP 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	101	103	100	98		100	98	96		97
3	107	103	99	96	106	101	98	95	99	96	94		97	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		94	91	89		92
5	101	95	90	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	96	91	87	84	89	86	83		88	85	83		87
7	95	88	84	81	94	87	83	81	86	83	80		85	82	80		84
8	92	85	81	78	91	85	81	78	84	80	78		83	80	77		82
9	89	82	78	75	88	82	78	75	81	78	75		80	77	75		80
10	87	80	76	73	86	80	76	73	79	75	73		78	75	73		78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	539685
5°	469189
10°	317913
15°	220381
20°	153580
25°	88372
30°	6930
35°	568
40°	287
45°	195
50°	167
55°	143
60°	164
65°	194
70°	164
75°	100
80°	149
85°	0



TEST NUMBER: P208912

CATALOG NUMBER: LDSQA6A45927D010TE LARH20SP 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	923.9	29.8
10°-20°	1391.5	44.8
20°-30°	766.6	24.7
30°-40°	15.8	0.5
40°-50°	2.5	0.1
50°-60°	1.9	0.1
60°-70°	1.7	0.1
70°-80°	0.7	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3082.0	99.3
0°-40°	3097.8	99.8
0°-60°	3102.3	99.9
0°-90°	3104.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3104.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12535	
5°	10856	924
15°	4944	1392
25°	1860	767
35°	11	16
45°	3	3
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P208912

CATALOG NUMBER: LDSQA6A45927D010TE LARH20SP 6LSQA1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	12534.6
2.5°	12159.6
5°	10855.8
7.5°	9227.3
10°	7271.6
12.5°	5988.1
15°	4944.1
17.5°	4168.0
20°	3351.9
22.5°	2621.6
25°	1860.2
27.5°	793.9
30°	139.4
32.5°	17.8
35°	10.8
37.5°	7.0
40°	5.1
42.5°	3.8
45°	3.2
47.5°	2.5
50°	2.5
52.5°	2.5
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.9
65°	1.9
67.5°	1.3
70°	1.3
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)