

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202840

Luminaire Tested: **LE_6B30D010 EC6B30508050 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508050 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3496.2 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202840

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202840

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202840

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.7	6.0
10°-20°	620.7	17.8
20°-30°	934.3	26.7
30°-40°	955.3	27.3
40°-50°	580.2	16.6
50°-60°	163.4	4.7
60°-70°	24.8	0.7
70°-80°	8.1	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1763.8	50.4
0°-40°	2719.1	77.8
0°-60°	3462.7	99.0
0°-90°	3496.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3496.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2172	
5°	2180	209
15°	2198	621
25°	2040	934
35°	1549	955
45°	746	580
55°	162	163
65°	22	25
75°	9	8
85°	0	1
90°	0	



TEST NUMBER: P202840

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2171.5
2.5°	2171.5
5°	2180.2
7.5°	2193.5
10°	2193.5
12.5°	2202.2
15°	2197.9
17.5°	2189.0
20°	2158.4
22.5°	2114.5
25°	2039.9
27.5°	1956.5
30°	1842.5
32.5°	1706.5
35°	1548.6
37.5°	1373.1
40°	1171.2
42.5°	960.8
45°	745.8
47.5°	552.8
50°	390.4
52.5°	263.2
55°	162.4
57.5°	96.5
60°	48.2
62.5°	30.8
65°	21.9
67.5°	17.5
70°	13.1
72.5°	8.8
75°	8.8
77.5°	4.4
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)