

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203266

Luminaire Tested: **LE_6B40D010 EC6B30509024 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509024 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2758.4 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203266

CATALOG NUMBER: LE_6B40D010 EC6B30509024 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203266

CATALOG NUMBER: LE_6B40D010 EC6B30509024 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92		
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53		
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49		
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203266

CATALOG NUMBER: LE_6B40D010 EC6B30509024 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.6	9.0
10°-20°	645.7	23.4
20°-30°	836.6	30.3
30°-40°	621.1	22.5
40°-50°	262.2	9.5
50°-60°	93.1	3.4
60°-70°	36.0	1.3
70°-80°	12.5	0.5
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1731.9	62.8
0°-40°	2353.0	85.3
0°-60°	2708.3	98.2
0°-90°	2758.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2758.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2730	
5°	2671	250
15°	2304	646
25°	1855	837
35°	985	621
45°	323	262
55°	98	93
65°	36	36
75°	12	13
85°	0	2
90°	0	



TEST NUMBER: P203266

CATALOG NUMBER: LE_6B40D010 EC6B30509024 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2729.6
2.5°	2721.8
5°	2670.6
7.5°	2595.8
10°	2505.1
12.5°	2406.6
15°	2304.2
17.5°	2190.0
20°	2087.6
22.5°	1981.2
25°	1855.2
27.5°	1681.9
30°	1477.1
32.5°	1236.8
35°	984.8
37.5°	772.0
40°	586.9
42.5°	437.2
45°	323.0
47.5°	236.4
50°	173.2
52.5°	130.0
55°	98.5
57.5°	74.9
60°	59.1
62.5°	43.4
65°	35.5
67.5°	27.6
70°	19.8
72.5°	15.8
75°	11.9
77.5°	7.9
80°	4.0
82.5°	4.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)