

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208982

Luminaire Tested: **LDSQA6A55835D010TE LARH40FL 6LSQA1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26677)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A55835D010TE LARH40FL 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5288.3 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 60.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208982

CATALOG NUMBER: LDSQA6A55835D010TE LARH40FL 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P208982

CATALOG NUMBER: LDSQA6A55835D010TE LARH40FL 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	109	112	110	108	107	106	105	104	103	101	100	99	98	98	96	96	96	96
2	110	107	103	101	108	105	102	100	102	99	97	99	97	95	96	95	93	92	92	92	92
3	107	101	98	94	105	100	97	94	98	95	92	95	93	91	93	91	89	88	88	88	88
4	103	97	93	89	101	96	92	89	94	90	88	92	89	87	90	88	86	85	85	85	85
5	99	93	88	85	98	92	88	84	90	87	84	89	85	83	87	85	82	81	81	81	81
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78	78	78	78
7	92	85	81	77	91	85	80	77	84	80	77	82	79	76	81	78	76	75	75	75	75
8	89	82	77	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72	72	72	72
9	86	79	74	71	85	79	74	71	78	74	71	77	73	71	76	73	71	70	70	70	70
10	84	76	72	69	83	76	71	69	75	71	68	74	71	68	74	70	68	67	67	67	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	589307
5°	513049
10°	463557
15°	423565
20°	310162
25°	153047
30°	33981
35°	6880
40°	1147
45°	341
50°	60
55°	68
60°	78
65°	92
70°	113
75°	0
80°	0
85°	0



TEST NUMBER: P208982

CATALOG NUMBER: LDSQA6A55835D010TE LARH40FL 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1100.4	20.8
10°-20°	2553.2	48.3
20°-30°	1497.7	28.3
30°-40°	129.6	2.4
40°-50°	5.6	0.1
50°-60°	0.8	0.0
60°-70°	0.9	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5151.3	97.4
0°-40°	5280.8	99.9
0°-60°	5287.3	100.0
0°-90°	5288.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5288.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13687	
5°	11871	###
15°	9502	2553
25°	3222	1498
35°	131	130
45°	6	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P208982

CATALOG NUMBER: LDSQA6A55835D010TE LARH40FL 6LSQA1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	13687.1
2.5°	12861.5
5°	11870.6
7.5°	11211.2
10°	10602.9
12.5°	10096.8
15°	9502.4
17.5°	8475.3
20°	6769.3
22.5°	4895.1
25°	3221.6
27.5°	1815.6
30°	683.5
32.5°	352.9
35°	130.9
37.5°	39.9
40°	20.4
42.5°	11.1
45°	5.6
47.5°	2.8
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)