

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208986

Luminaire Tested: **LDSQA6A55935D010TE LARH40FL 6LSQA1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208986
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26677)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A55935D010TE LARH40FL 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4521.3 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 60.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208986

CATALOG NUMBER: LDSQA6A55935D010TE LARH40FL 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P208986

CATALOG NUMBER: LDSQA6A55935D010TE LARH40FL 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	109	112	110	108	107	106	105	104	103	101	100	99	98	98	96			
2	110	107	103	101	108	105	102	100	102	99	97	99	97	95	96	95	93	92			
3	107	101	98	94	105	100	97	94	98	95	92	95	93	91	93	91	89	88			
4	103	97	93	89	101	96	92	89	94	90	88	92	89	87	90	88	86	85			
5	99	93	88	85	98	92	88	84	90	87	84	89	85	83	87	85	82	81			
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78			
7	92	85	81	77	91	85	80	77	84	80	77	82	79	76	81	78	76	75			
8	89	82	77	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72			
9	86	79	74	71	85	79	74	71	78	74	71	77	73	71	76	73	71	70			
10	84	76	72	69	83	76	71	69	75	71	68	74	71	68	74	70	68	67			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	503824
5°	438624
10°	396316
15°	362123
20°	265168
25°	130848
30°	29054
35°	5887
40°	984
45°	292
50°	54
55°	60
60°	69
65°	82
70°	101
75°	0
80°	0
85°	0



TEST NUMBER: P208986

CATALOG NUMBER: LDSQA6A55935D010TE LARH40FL 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	940.8	20.8
10°-20°	2182.9	48.3
20°-30°	1280.4	28.3
30°-40°	110.8	2.5
40°-50°	4.8	0.1
50°-60°	0.7	0.0
60°-70°	0.8	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4404.0	97.4
0°-40°	4514.8	99.9
0°-60°	4520.4	100.0
0°-90°	4521.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4521.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11702	
5°	10149	941
15°	8124	2183
25°	2754	1280
35°	112	111
45°	5	5
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P208986

CATALOG NUMBER: LDSQA6A55935D010TE LARH40FL 6LSQA1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	11701.7
2.5°	10995.8
5°	10148.6
7.5°	9584.9
10°	9064.9
12.5°	8632.1
15°	8124.0
17.5°	7245.9
20°	5787.3
22.5°	4185.1
25°	2754.3
27.5°	1552.2
30°	584.4
32.5°	301.7
35°	112.0
37.5°	34.1
40°	17.5
42.5°	9.5
45°	4.8
47.5°	2.4
50°	0.8
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)