

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202644

Luminaire Tested: **LE_6B40D010 EC6B30508030 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508030 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4096.9 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202644

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202644

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69			
6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56			
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202644

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	418.2	10.2
10°-20°	1073.4	26.2
20°-30°	1318.4	32.2
30°-40°	904.0	22.1
40°-50°	290.6	7.1
50°-60°	58.9	1.4
60°-70°	23.2	0.6
70°-80°	8.7	0.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2810.0	68.6
0°-40°	3714.0	90.7
0°-60°	4063.5	99.2
0°-90°	4096.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4096.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4556	
5°	4469	418
15°	3840	1073
25°	2909	1318
35°	1442	904
45°	344	291
55°	59	59
65°	24	23
75°	7	9
85°	0	1
90°	0	



TEST NUMBER: P202644

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4556.0
2.5°	4528.1
5°	4469.1
7.5°	4357.9
10°	4208.4
12.5°	4024.2
15°	3840.0
17.5°	3635.0
20°	3409.1
22.5°	3172.9
25°	2908.8
27.5°	2616.8
30°	2248.4
32.5°	1841.9
35°	1442.2
37.5°	1077.2
40°	775.0
42.5°	528.2
45°	344.0
47.5°	212.0
50°	128.6
52.5°	79.9
55°	59.1
57.5°	45.1
60°	34.8
62.5°	27.8
65°	24.4
67.5°	17.4
70°	13.9
72.5°	10.4
75°	7.0
77.5°	7.0
80°	3.5
82.5°	3.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)