

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203674

Luminaire Tested: **LE\_6B40D010 EC6B30508030 6LBNH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203674  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30508030 6LBNH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3284.7 lumens  
Efficiency: N/A  
Efficacy: 78.6 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203674

CATALOG NUMBER: LE\_6B40D010 EC6B30508030 6LBNH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203674

CATALOG NUMBER: LE\_6B40D010 EC6B30508030 6LBNH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203674

CATALOG NUMBER: LE\_6B40D010 EC6B30508030 6LBNH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	378.6	11.5
10°-20°	903.0	27.5
20°-30°	1034.4	31.5
30°-40°	695.0	21.2
40°-50°	198.6	6.0
50°-60°	48.6	1.5
60°-70°	18.5	0.6
70°-80°	7.1	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2316.0	70.5
0°-40°	3011.1	91.7
0°-60°	3258.3	99.2
0°-90°	3284.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3284.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4210	
5°	4091	379
15°	3240	903
25°	2258	1034
35°	1108	695
45°	228	199
55°	54	49
65°	18	18
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P203674

CATALOG NUMBER: LE\_6B40D010 EC6B30508030 6LBNH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4210.5
2.5°	4180.6
5°	4090.8
7.5°	3929.0
10°	3731.4
12.5°	3479.9
15°	3240.2
17.5°	2988.8
20°	2737.1
22.5°	2497.6
25°	2258.0
27.5°	2036.4
30°	1778.9
32.5°	1437.5
35°	1108.0
37.5°	808.6
40°	557.0
42.5°	365.4
45°	227.6
47.5°	137.8
50°	83.9
52.5°	65.9
55°	53.9
57.5°	41.9
60°	30.0
62.5°	24.0
65°	18.0
67.5°	12.0
70°	12.0
72.5°	6.0
75°	6.0
77.5°	6.0
80°	6.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)