

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204086

Luminaire Tested: **LE_6B40D010 EC6B30508030 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508030 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3769.3 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204086

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204086

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204086

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	287.0	7.6
10°-20°	760.9	20.2
20°-30°	1015.8	26.9
30°-40°	819.5	21.7
40°-50°	392.7	10.4
50°-60°	232.8	6.2
60°-70°	154.8	4.1
70°-80°	82.9	2.2
80°-90°	22.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2063.7	54.7
0°-40°	2883.2	76.5
0°-60°	3508.7	93.1
0°-90°	3769.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3769.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3091	
5°	3055	287
15°	2708	761
25°	2222	1016
35°	1312	820
45°	485	393
55°	258	233
65°	156	155
75°	78	83
85°	18	23
90°	0	



TEST NUMBER: P204086

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3091.1
2.5°	3091.1
5°	3055.2
7.5°	2995.4
10°	2911.5
12.5°	2821.6
15°	2707.8
17.5°	2600.0
20°	2480.1
22.5°	2354.4
25°	2222.5
27.5°	2084.8
30°	1887.0
32.5°	1611.5
35°	1312.0
37.5°	1036.4
40°	802.8
42.5°	623.0
45°	485.2
47.5°	383.4
50°	323.5
52.5°	287.5
55°	257.6
57.5°	233.6
60°	203.6
62.5°	179.8
65°	155.8
67.5°	131.8
70°	113.9
72.5°	95.9
75°	77.9
77.5°	59.9
80°	47.9
82.5°	36.0
85°	18.0
87.5°	6.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)