

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204602

Luminaire Tested: **LE_6B40D010 EC6B30508030 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508030 6LBSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5671.6 lumens
Efficiency: N/A
Efficacy: 135.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204602

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204602

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204602

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.5	3.8
10°-20°	617.2	10.9
20°-30°	929.5	16.4
30°-40°	1106.0	19.5
40°-50°	1104.0	19.5
50°-60°	897.8	15.8
60°-70°	552.3	9.7
70°-80°	214.0	3.8
80°-90°	34.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1763.2	31.1
0°-40°	2869.2	50.6
0°-60°	4871.0	85.9
0°-90°	5671.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5671.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2285	
5°	2278	217
15°	2191	617
25°	2023	930
35°	1771	1106
45°	1435	1104
55°	1005	898
65°	554	552
75°	195	214
85°	27	34
90°	0	



TEST NUMBER: P204602

CATALOG NUMBER: LE_6B40D010 EC6B30508030 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2285.1
2.5°	2288.5
5°	2278.4
7.5°	2265.0
10°	2248.1
12.5°	2217.9
15°	2191.0
17.5°	2150.8
20°	2107.0
22.5°	2066.8
25°	2023.0
27.5°	1962.5
30°	1902.0
32.5°	1844.9
35°	1771.0
37.5°	1690.4
40°	1616.4
42.5°	1525.6
45°	1434.9
47.5°	1337.5
50°	1233.2
52.5°	1125.8
55°	1004.8
57.5°	887.1
60°	772.9
62.5°	662.0
65°	554.5
67.5°	453.6
70°	359.6
72.5°	272.2
75°	194.9
77.5°	127.8
80°	77.2
82.5°	47.0
85°	26.9
87.5°	13.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)