

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202547

Luminaire Tested: **LE\_6B40D010 EC6B30509030 6LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202547  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B40D010 EC6B30509030 6LBSWMH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4686.9 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202547

CATALOG NUMBER: LE\_6B40D010 EC6B30509030 6LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202547

CATALOG NUMBER: LE\_6B40D010 EC6B30509030 6LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77				77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42				42
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38				38
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35				35
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32				32

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202547

CATALOG NUMBER: LE\_6B40D010 EC6B30509030 6LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	250.7	5.3
10°-20°	655.5	14.0
20°-30°	869.2	18.5
30°-40°	927.1	19.8
40°-50°	866.6	18.5
50°-60°	660.8	14.1
60°-70°	359.5	7.7
70°-80°	96.4	2.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1775.4	37.9
0°-40°	2702.5	57.7
0°-60°	4229.9	90.2
0°-90°	4686.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4686.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2710	
5°	2673	251
15°	2337	655
25°	1892	869
35°	1482	927
45°	1128	867
55°	744	661
65°	359	359
75°	83	96
85°	0	1
90°	0	



TEST NUMBER: P202547

CATALOG NUMBER: LE\_6B40D010 EC6B30509030 6LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2710.2
2.5°	2701.6
5°	2672.9
7.5°	2612.6
10°	2543.8
12.5°	2446.1
15°	2337.0
17.5°	2227.9
20°	2110.2
22.5°	1998.2
25°	1892.0
27.5°	1780.0
30°	1673.8
32.5°	1570.5
35°	1481.5
37.5°	1392.5
40°	1300.6
42.5°	1217.2
45°	1128.2
47.5°	1030.8
50°	938.9
52.5°	841.2
55°	743.6
57.5°	637.4
60°	539.8
62.5°	447.9
65°	358.9
67.5°	278.5
70°	203.9
72.5°	140.6
75°	83.2
77.5°	37.4
80°	8.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)