

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P209002

Luminaire Tested: **LDSQA6A75935D010TE LARH40FL 6LSQA1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P209002
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26677)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A75935D010TE LARH40FL 6LSQA1H
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6140.8 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P209002

CATALOG NUMBER: LDSQA6A75935D010TE LARH40FL 6LSQA1H

Luminous Intensity Polar Plot





TEST NUMBER: P209002

CATALOG NUMBER: LDSQA6A75935D010TE LARH40FL 6LSQA1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	109	112	110	108	107	106	105	104	103	101	100	99	98	98	96																												
2	110	107	103	101	108	105	102	100	102	99	97	99	97	95	96	95	93	92																												
3	107	101	98	94	105	100	97	94	98	95	92	95	93	91	93	91	89	88																												
4	103	97	93	89	101	96	92	89	94	90	88	92	89	87	90	88	86	85																												
5	99	93	88	85	98	92	88	84	90	87	84	89	85	83	87	85	82	81																												
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																												
7	92	85	81	77	91	85	80	77	84	80	77	82	79	76	81	78	76	75																												
8	89	82	77	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																												
9	86	79	74	71	85	79	74	71	78	74	71	77	73	71	76	73	71	70																												
10	84	76	72	69	83	76	71	69	75	71	68	74	71	68	74	70	68	67																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	684297
5°	595742
10°	538275
15°	491835
20°	360155
25°	177718
30°	39460
35°	7995
40°	1332
45°	396
50°	74
55°	83
60°	95
65°	112
70°	138
75°	0
80°	0
85°	0



TEST NUMBER: P209002

CATALOG NUMBER: LDSQA6A75935D010TE LARH40FL 6LSQA1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1277.7	20.8
10°-20°	2964.8	48.3
20°-30°	1739.1	28.3
30°-40°	150.5	2.5
40°-50°	6.6	0.1
50°-60°	1.0	0.0
60°-70°	1.1	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5981.6	97.4
0°-40°	6132.1	99.9
0°-60°	6139.6	100.0
0°-90°	6140.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6140.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15893	
5°	13784	###
15°	11034	2965
25°	3741	1739
35°	152	150
45°	6	7
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P209002

CATALOG NUMBER: LDSQA6A75935D010TE LARH40FL 6LSQA1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	15893.3
2.5°	14934.6
5°	13783.9
7.5°	13018.3
10°	12311.9
12.5°	11724.2
15°	11034.0
17.5°	9841.4
20°	7860.4
22.5°	5684.2
25°	3740.9
27.5°	2108.2
30°	793.7
32.5°	409.8
35°	152.1
37.5°	46.4
40°	23.7
42.5°	12.9
45°	6.5
47.5°	3.2
50°	1.1
52.5°	1.1
55°	1.1
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1
67.5°	1.1
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)