

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202959

Luminaire Tested: **LE_6B40D010 EC6B30509030 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509030 6LBWGPH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2968.7 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202959

CATALOG NUMBER: LE_6B40D010 EC6B30509030 6LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P202959

CATALOG NUMBER: LE_6B40D010 EC6B30509030 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	81	71	64	59	80	70	63	59	68	62	58	67	62	58	65	61	57	56			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51			
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47			
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43			
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202959

CATALOG NUMBER: LE_6B40D010 EC6B30509030 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.1	6.4
10°-20°	533.0	18.0
20°-30°	762.6	25.7
30°-40°	760.1	25.6
40°-50°	484.1	16.3
50°-60°	178.6	6.0
60°-70°	44.7	1.5
70°-80°	13.5	0.5
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1485.7	50.0
0°-40°	2245.8	75.7
0°-60°	2908.5	98.0
0°-90°	2968.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2968.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2018	
5°	2008	190
15°	1895	533
25°	1665	763
35°	1236	760
45°	623	484
55°	189	179
65°	41	45
75°	10	13
85°	0	2
90°	0	



TEST NUMBER: P202959

CATALOG NUMBER: LE_6B40D010 EC6B30509030 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2017.6
2.5°	2017.6
5°	2007.5
7.5°	1987.0
10°	1961.5
12.5°	1930.9
15°	1895.1
17.5°	1849.1
20°	1798.0
22.5°	1741.9
25°	1665.2
27.5°	1583.5
30°	1476.2
32.5°	1363.9
35°	1236.1
37.5°	1082.9
40°	924.5
42.5°	771.2
45°	623.1
47.5°	490.4
50°	367.8
52.5°	270.8
55°	189.0
57.5°	122.6
60°	81.8
62.5°	56.2
65°	40.9
67.5°	30.6
70°	25.5
72.5°	15.4
75°	10.2
77.5°	10.2
80°	5.1
82.5°	5.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)