

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204700

Luminaire Tested: **LD6B30D010 EU6B30509035 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509035 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2780.2 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204700

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204700

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	65	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204700

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.1	3.8
10°-20°	302.5	10.9
20°-30°	455.6	16.4
30°-40°	542.2	19.5
40°-50°	541.2	19.5
50°-60°	440.1	15.8
60°-70°	270.8	9.7
70°-80°	104.9	3.8
80°-90°	16.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	864.3	31.1
0°-40°	1406.5	50.6
0°-60°	2387.8	85.9
0°-90°	2780.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2780.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1120	
5°	1117	106
15°	1074	303
25°	992	456
35°	868	542
45°	703	541
55°	492	440
65°	272	271
75°	96	105
85°	13	17
90°	0	



TEST NUMBER: P204700

CATALOG NUMBER: LD6B30D010 EU6B30509035 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1120.2
2.5°	1121.8
5°	1116.9
7.5°	1110.3
10°	1102.0
12.5°	1087.2
15°	1074.0
17.5°	1054.3
20°	1032.9
22.5°	1013.1
25°	991.7
27.5°	962.0
30°	932.4
32.5°	904.4
35°	868.1
37.5°	828.6
40°	792.3
42.5°	747.9
45°	703.4
47.5°	655.6
50°	604.6
52.5°	551.8
55°	492.5
57.5°	434.9
60°	378.9
62.5°	324.5
65°	271.8
67.5°	222.4
70°	176.3
72.5°	133.4
75°	95.5
77.5°	62.6
80°	37.9
82.5°	23.1
85°	13.2
87.5°	6.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)