

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204097

Luminaire Tested: **LE_6B40D010 EC6B30509730 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509730 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2813.7 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204097

CATALOG NUMBER: LE_6B40D010 EC6B30509730 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204097

CATALOG NUMBER: LE_6B40D010 EC6B30509730 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204097

CATALOG NUMBER: LE_6B40D010 EC6B30509730 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.3	7.6
10°-20°	568.0	20.2
20°-30°	758.3	26.9
30°-40°	611.8	21.7
40°-50°	293.2	10.4
50°-60°	173.7	6.2
60°-70°	115.5	4.1
70°-80°	61.9	2.2
80°-90°	17.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1540.5	54.8
0°-40°	2152.3	76.5
0°-60°	2619.2	93.1
0°-90°	2813.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2813.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2308	
5°	2281	214
15°	2021	568
25°	1659	758
35°	979	612
45°	362	293
55°	192	174
65°	116	116
75°	58	62
85°	13	17
90°	0	



TEST NUMBER: P204097

CATALOG NUMBER: LE_6B40D010 EC6B30509730 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2307.6
2.5°	2307.6
5°	2280.8
7.5°	2236.0
10°	2173.4
12.5°	2106.4
15°	2021.4
17.5°	1940.9
20°	1851.4
22.5°	1757.5
25°	1659.1
27.5°	1556.2
30°	1408.8
32.5°	1203.0
35°	979.4
37.5°	773.6
40°	599.2
42.5°	465.1
45°	362.2
47.5°	286.2
50°	241.5
52.5°	214.6
55°	192.2
57.5°	174.4
60°	152.0
62.5°	134.1
65°	116.2
67.5°	98.4
70°	85.0
72.5°	71.5
75°	58.1
77.5°	44.8
80°	35.8
82.5°	26.9
85°	13.4
87.5°	4.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)