

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843972

Luminaire Tested: **LD6C10DE010B2750 EU6C10B35 6LBNH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C10DE010B2750 EU6C10B35 6LBNH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 754.0 lumens
Efficiency: N/A
Efficacy: 56.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843972

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B35 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P843972

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B35 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52995
5°	51684
10°	47689
15°	42219
20°	36654
25°	31351
30°	25852
35°	17025
40°	9153
45°	4047
50°	1637
55°	1185
60°	757
65°	532
70°	433
75°	297
80°	442
85°	0



TEST NUMBER: P843972

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B35 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.9	11.5
10°-20°	207.3	27.5
20°-30°	237.5	31.5
30°-40°	159.6	21.2
40°-50°	45.6	6.0
50°-60°	11.1	1.5
60°-70°	4.2	0.6
70°-80°	1.6	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.7	70.5
0°-40°	691.3	91.7
0°-60°	748.0	99.2
0°-90°	754.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	754.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	967	
5°	939	87
15°	744	207
25°	518	237
35°	254	160
45°	52	46
55°	12	11
65°	4	4
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P843972

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B35 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	966.7
2.5°	959.8
5°	939.2
7.5°	902.1
10°	856.7
12.5°	798.8
15°	743.9
17.5°	686.2
20°	628.3
22.5°	573.4
25°	518.3
27.5°	467.5
30°	408.4
32.5°	330.0
35°	254.4
37.5°	185.6
40°	127.9
42.5°	83.9
45°	52.2
47.5°	31.6
50°	19.2
52.5°	15.1
55°	12.4
57.5°	9.6
60°	6.9
62.5°	5.5
65°	4.1
67.5°	2.7
70°	2.7
72.5°	1.4
75°	1.4
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)