

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843973

Luminaire Tested: **LD6C10DE010B2750 EU6C10B35 6LBNLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P843973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C10DE010B2750 EU6C10B35 6LBNI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 953.9 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843973

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B35 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P843973

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B35 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119069
5°	111352
10°	90813
15°	66828
20°	46058
25°	34194
30°	25687
35°	16015
40°	7772
45°	2667
50°	350
55°	258
60°	153
65°	182
70°	224
75°	0
80°	0
85°	0



TEST NUMBER: P843973

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B35 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.6	18.9
10°-20°	324.1	34.0
20°-30°	262.1	27.5
30°-40°	151.0	15.8
40°-50°	31.9	3.3
50°-60°	2.7	0.3
60°-70°	1.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	766.8	80.4
0°-40°	917.7	96.2
0°-60°	952.4	99.8
0°-90°	953.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	953.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2172	
5°	2024	181
15°	1178	324
25°	565	262
35°	239	151
45°	34	32
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843973

CATALOG NUMBER: LD6C10DE010B2750 EU6C10B35 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2172.0
2.5°	2145.9
5°	2023.5
7.5°	1847.4
10°	1631.4
12.5°	1409.9
15°	1177.5
17.5°	953.2
20°	789.5
22.5°	664.4
25°	565.3
27.5°	481.4
30°	405.8
32.5°	321.9
35°	239.3
37.5°	166.5
40°	108.6
42.5°	66.0
45°	34.4
47.5°	13.7
50°	4.1
52.5°	4.1
55°	2.7
57.5°	2.7
60°	1.4
62.5°	1.4
65°	1.4
67.5°	1.4
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)