

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203675

Luminaire Tested: **LE_6B40D010 EC6B30508035 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203675
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508035 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3365.9 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203675

CATALOG NUMBER: LE_6B40D010 EC6B30508035 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203675

CATALOG NUMBER: LE_6B40D010 EC6B30508035 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203675

CATALOG NUMBER: LE_6B40D010 EC6B30508035 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	388.0	11.5
10°-20°	925.3	27.5
20°-30°	1060.1	31.5
30°-40°	712.2	21.2
40°-50°	203.5	6.0
50°-60°	49.8	1.5
60°-70°	18.9	0.6
70°-80°	7.2	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2373.4	70.5
0°-40°	3085.7	91.7
0°-60°	3338.9	99.2
0°-90°	3365.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3365.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4315	
5°	4192	388
15°	3320	925
25°	2314	1060
35°	1136	712
45°	233	203
55°	55	50
65°	18	19
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P203675

CATALOG NUMBER: LE_6B40D010 EC6B30508035 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4314.9
2.5°	4284.1
5°	4192.1
7.5°	4026.4
10°	3823.9
12.5°	3566.0
15°	3320.5
17.5°	3062.8
20°	2805.0
22.5°	2559.5
25°	2313.9
27.5°	2086.9
30°	1822.9
32.5°	1473.0
35°	1135.5
37.5°	828.6
40°	570.8
42.5°	374.4
45°	233.2
47.5°	141.1
50°	85.9
52.5°	67.5
55°	55.2
57.5°	43.0
60°	30.8
62.5°	24.5
65°	18.4
67.5°	12.2
70°	12.2
72.5°	6.1
75°	6.1
77.5°	6.1
80°	6.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)