

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205530

Luminaire Tested: **LE_6B40D010 EC6B30509035 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205530
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509035 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2524.0 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205530

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205530

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68		
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205530

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.6	9.6
10°-20°	627.0	24.8
20°-30°	798.9	31.7
30°-40°	564.6	22.4
40°-50°	206.1	8.2
50°-60°	57.1	2.3
60°-70°	20.7	0.8
70°-80°	7.4	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1667.4	66.1
0°-40°	2232.0	88.4
0°-60°	2495.2	98.9
0°-90°	2524.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2524.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2630	
5°	2584	242
15°	2233	627
25°	1774	799
35°	897	565
45°	250	206
55°	61	57
65°	20	21
75°	5	7
85°	0	1
90°	0	



TEST NUMBER: P205530

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2630.1
2.5°	2620.0
5°	2584.2
7.5°	2512.9
10°	2436.5
12.5°	2334.5
15°	2232.6
17.5°	2130.6
20°	2028.6
22.5°	1906.4
25°	1773.9
27.5°	1590.4
30°	1386.4
32.5°	1141.8
35°	897.1
37.5°	683.0
40°	499.5
42.5°	361.9
45°	249.8
47.5°	168.2
50°	112.1
52.5°	76.5
55°	61.1
57.5°	45.9
60°	35.6
62.5°	25.5
65°	20.4
67.5°	15.2
70°	10.2
72.5°	10.2
75°	5.1
77.5°	5.1
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)