

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204402

Luminaire Tested: **LE_6B40D010 EC6B30509035 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30509035 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4322.3 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204402
CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204402

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88	88	88	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66	66	66	66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50	50	50	50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45	45	45	45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40	40	40	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36	36	36	36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32	32	32	32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204402

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	4.4
10°-20°	530.6	12.3
20°-30°	773.8	17.9
30°-40°	882.5	20.4
40°-50°	846.5	19.6
50°-60°	648.3	15.0
60°-70°	355.7	8.2
70°-80°	94.6	2.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1493.4	34.6
0°-40°	2375.9	55.0
0°-60°	3870.6	89.5
0°-90°	4322.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4322.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2008	
5°	1992	189
15°	1883	531
25°	1681	774
35°	1411	882
45°	1100	846
55°	726	648
65°	358	356
75°	83	95
85°	0	1
90°	0	



TEST NUMBER: P204402

CATALOG NUMBER: LE_6B40D010 EC6B30509035 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2007.5
2.5°	2002.4
5°	1992.0
7.5°	1976.4
10°	1955.6
12.5°	1919.4
15°	1883.0
17.5°	1841.5
20°	1794.9
22.5°	1737.8
25°	1680.8
27.5°	1623.6
30°	1551.0
32.5°	1483.6
35°	1411.0
37.5°	1338.4
40°	1265.8
42.5°	1187.9
45°	1099.8
47.5°	1011.5
50°	918.1
52.5°	819.6
55°	726.2
57.5°	632.9
60°	534.2
62.5°	440.9
65°	357.9
67.5°	274.9
70°	202.2
72.5°	134.9
75°	83.0
77.5°	36.2
80°	10.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)