

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844018

Luminaire Tested: **LD6C15DE010B2750 EU6C15B27 6LBMB**

Issue Date: 5/7/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P844018  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C15DE010B2750 EU6C15B27 6LBMB  
Description:  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 667.4 lumens  
Efficiency: N/A  
Efficacy: 39.3 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 17  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844018

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B27 6LBMB

### Luminous Intensity Polar Plot





TEST NUMBER: P844018

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B27 6LBMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27295
5°	26948
10°	26029
15°	24915
20°	23680
25°	22048
30°	18997
35°	14415
40°	10534
45°	7993
50°	6516
55°	5725
60°	5252
65°	4774
70°	4280
75°	3897
80°	3504
85°	2830



TEST NUMBER: P844018

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B27 6LBMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.0	6.9
10°-20°	123.2	18.5
20°-30°	165.4	24.8
30°-40°	135.7	20.3
40°-50°	81.5	12.2
50°-60°	54.2	8.1
60°-70°	36.3	5.4
70°-80°	19.5	2.9
80°-90°	5.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.7	50.1
0°-40°	470.3	70.5
0°-60°	606.0	90.8
0°-90°	667.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	667.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	498	
5°	490	46
15°	439	123
25°	364	165
35°	215	136
45°	103	82
55°	60	54
65°	37	36
75°	18	20
85°	4	5
90°	0	



TEST NUMBER: P844018

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B27 6LBMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	497.9
2.5°	494.2
5°	489.7
7.5°	479.5
10°	467.6
12.5°	452.9
15°	439.0
17.5°	422.5
20°	405.9
22.5°	387.5
25°	364.5
27.5°	336.9
30°	300.1
32.5°	258.6
35°	215.4
37.5°	178.5
40°	147.2
42.5°	122.5
45°	103.1
47.5°	87.5
50°	76.4
52.5°	67.2
55°	59.9
57.5°	53.4
60°	47.9
62.5°	41.5
65°	36.8
67.5°	31.3
70°	26.7
72.5°	22.1
75°	18.4
77.5°	14.7
80°	11.1
82.5°	8.2
85°	4.5
87.5°	1.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)