

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P252807

Luminaire Tested: **LE_6B40D010 EC6B30508040 6LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B40D010 EC6B30508040 6LBBA1MW
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6882.4 lumens
Efficiency: N/A
Efficacy: 160.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 43
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252807

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252807

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56			
6	78	67	60	54	77	66	59	54	65	58	54	63	57	53	62	57	53	51			
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	47			
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	307975
5°	305143
10°	298430
15°	288945
20°	277280
25°	260298
30°	225247
35°	175376
40°	133293
45°	103899
50°	86181
55°	77346
60°	70434
65°	64991
70°	59705
75°	55329
80°	50006
85°	45737



TEST NUMBER: P252807

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.8	6.4
10°-20°	1202.0	17.5
20°-30°	1637.0	23.8
30°-40°	1385.3	20.1
40°-50°	888.7	12.9
50°-60°	611.5	8.9
60°-70°	417.8	6.1
70°-80°	232.4	3.4
80°-90°	68.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3278.8	47.6
0°-40°	4664.1	67.8
0°-60°	6164.3	89.6
0°-90°	6882.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6882.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4721	
5°	4659	440
15°	4278	1202
25°	3616	1637
35°	2202	1385
45°	1126	889
55°	680	612
65°	421	418
75°	220	232
85°	61	68
90°	0	



TEST NUMBER: P252807

CATALOG NUMBER: LE_6B40D010 EC6B30508040 6LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4720.6
2.5°	4702.6
5°	4659.4
7.5°	4591.0
10°	4504.8
12.5°	4396.8
15°	4278.0
17.5°	4141.2
20°	3993.8
22.5°	3828.2
25°	3616.0
27.5°	3328.1
30°	2990.0
32.5°	2601.4
35°	2202.0
37.5°	1853.0
40°	1565.1
42.5°	1324.1
45°	1126.1
47.5°	971.5
50°	849.1
52.5°	755.6
55°	680.0
57.5°	608.0
60°	539.8
62.5°	478.5
65°	421.0
67.5°	363.4
70°	313.0
72.5°	262.6
75°	219.5
77.5°	176.2
80°	133.1
82.5°	97.1
85°	61.1
87.5°	25.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)