

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844038

Luminaire Tested: **LD6C15DE010B2750 EU6C15B30 6LBMLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P844038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15DE010B2750 EU6C15B30 6LBMLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1352.7 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844038

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P844038

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92800
5°	91916
10°	87106
15°	79081
20°	69884
25°	60409
30°	47229
35°	28964
40°	14864
45°	5900
50°	1919
55°	659
60°	570
65°	454
70°	272
75°	360
80°	0
85°	0



TEST NUMBER: P844038

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.0	11.5
10°-20°	388.3	28.7
20°-30°	451.3	33.4
30°-40°	276.4	20.4
40°-50°	68.6	5.1
50°-60°	8.0	0.6
60°-70°	3.0	0.2
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	995.5	73.6
0°-40°	1271.9	94.0
0°-60°	1348.6	99.7
0°-90°	1352.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1352.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1693	
5°	1670	156
15°	1393	388
25°	999	451
35°	433	276
45°	76	69
55°	7	8
65°	4	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P844038

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1692.8
2.5°	1691.2
5°	1670.3
7.5°	1625.4
10°	1564.8
12.5°	1485.1
15°	1393.4
17.5°	1294.8
20°	1197.9
22.5°	1100.9
25°	998.7
27.5°	881.0
30°	746.1
32.5°	588.5
35°	432.8
37.5°	304.6
40°	207.7
42.5°	129.8
45°	76.1
47.5°	43.3
50°	22.5
52.5°	10.4
55°	6.9
57.5°	5.2
60°	5.2
62.5°	3.5
65°	3.5
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)