

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844040

Luminaire Tested: **LD6C15DE010B2750 EU6C15B30 6LBNH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15DE010B2750 EU6C15B30 6LBNH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 950.8 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844040

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P844040

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66815
5°	65161
10°	60130
15°	53235
20°	46222
25°	39535
30°	32600
35°	21469
40°	11543
45°	5109
50°	2072
55°	1501
60°	954
65°	675
70°	561
75°	360
80°	537
85°	0



TEST NUMBER: P844040

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	11.5
10°-20°	261.4	27.5
20°-30°	299.4	31.5
30°-40°	201.2	21.2
40°-50°	57.5	6.0
50°-60°	14.1	1.5
60°-70°	5.3	0.6
70°-80°	2.0	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.4	70.5
0°-40°	871.6	91.7
0°-60°	943.2	99.2
0°-90°	950.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	950.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1219	
5°	1184	110
15°	938	261
25°	654	299
35°	321	201
45°	66	58
55°	16	14
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P844040

CATALOG NUMBER: LD6C15DE010B2750 EU6C15B30 6LBNH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1218.8
2.5°	1210.1
5°	1184.1
7.5°	1137.3
10°	1080.2
12.5°	1007.3
15°	938.0
17.5°	865.1
20°	792.3
22.5°	723.0
25°	653.6
27.5°	589.4
30°	515.0
32.5°	416.1
35°	320.8
37.5°	234.1
40°	161.3
42.5°	105.8
45°	65.9
47.5°	39.9
50°	24.3
52.5°	19.0
55°	15.7
57.5°	12.2
60°	8.7
62.5°	6.9
65°	5.2
67.5°	3.5
70°	3.5
72.5°	1.7
75°	1.7
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)